

GLOW PLUGS

of high efficiency and of long life

- R1 v. hot - from ~~0,8~~ 0,8 to 2 c.c.
- R2 hot - from 2 to 3,5 c.c.
- R3 med. - from 3,5 to 6 c.c.
- R4 cold - from 6 to 10 c.c.
- R5 very cold - for Nitro Fuel
or for R.C.
- R6 cold - for Nitro Fuel
from 10 c.c. to 13 c.c.
- R7 cold - for Nitro Fuel
from 13 c.c. to 15 c.c.
- R8 cold - for Nitro Fuel
from 15 c.c. to 30 c.c.
- R.C. hot - from 2,5 to 6 c.c.
- R.C. cold - from 6 to 10 c.c.
- RFS hot - only for four stroke
engine

USE 1,5 VOLT
ROSSI - ITALY