

PART NO.: CH-0408-03135-65

TECHNICAL REQUIREMENTS:

- (1) Rated Voltage: 3.7V DC;
- (2) No Load Speed: 60000rpm \pm 10%;
- (3) No Load Current: 80mA max.;
- (4) Starting Voltage: 2.0V DC max.;
- (5) Starting Current: 280mA max.

NOTES:

1. DIMENSIONS, MODIFICATIONS OR CHANGES NOT INDICATED ON THIS DRAWING DO NOT APPLY UNLESS CONFIRMED BY US IN WRITING.
2. THIS DIM, APPLIES ONLY WHEN MOTOR SHAFT IS IN EXTREME RIGHT POSITION.
3. SHAFT END PLAY 0.05~0.35mm.

