	<b>Title:</b>	<b>Date:</b>	<b>Rev:</b>	<b>Page:</b>	<b>File Name:</b>
	<b>Material Safety Data Sheet for All Optima Batteries</b>	<b>10/17/11</b>	<b>M</b>	<b>1 of 5</b>	<b>MSDS battery</b>

MSDS No. L 8A
Date Issued <b>Feb. 20, 1990</b>
Date Revised <b>Oct. 17, 2011</b>

Chemical/Trade Name (identity used on label) <b>Sealed Lead Acid Battery/ OPTIMA BATTERY™</b>	Chemical Family/Classification <b>Electric Storage Battery</b>	HMIS Rating for Sealed, Lead Acid Battery <b>0 0 0</b> ; For sulfuric acid <b>3 0 2</b>
Synonyms/Common Name <b>Sealed Lead Acid Battery</b>	DOT, IATA and IMO Description <b>Non-Spillable Battery , Exempt from UN2800 Classification</b>	
Company Name <b>OPTIMA Batteries, Inc.</b>	Address <b>5757 N. Green Bay Avenue Milwaukee, WI 53209</b>	
Division or Department <b>Wholly- owned subsidiary of Johnson Controls Inc.</b>		
CONTACT		TELEPHONE NUMBER
Questions Concerning MSDS <b>OPTIMA Batteries, Environmental, Health &amp; Safety Department</b>	<b>Day: (800) 333-2222, Ext. 3138</b>	
Transportation Emergencies <b>CHEMTREC</b>	<b>24 Hours: (800) 424-9300 International: (703) 527-3887 (Collect)</b>	

**NOTE: The OPTIMA sealed lead acid battery is considered an article as defined by 29 CFR 1910.1200 © OSHA Hazard Communication Standard. The information on this MSDS is supplied at customer's request for information only.**


**II. Hazardous Ingredients**

Material	% by Wt.	CAS Number	Eight Hour Exposure Limits		
			OSHA PEL	ACGIH TLV	NIOSH REL
Specific Chemical Identity <b>Lead &amp; lead compounds</b>	63-81	7439-92-1	50 µg/m <sup>3</sup>	150 µg/m <sup>3</sup>	100 µg/m <sup>3</sup>
Specific Chemical Identity <b>Sulfuric Acid (35%)</b> Common Name <b>Battery Electrolyte (Acid)</b>	17 - 25	7664-93-9	1mg/m <sup>3</sup>	0.2 mg/m <sup>3</sup> (respirable thoracic fraction)	1 mg/m <sup>3</sup>
Common Name <b>Case Material Polypropylene</b>	2-6	9010-79-1	--	--	--
Common Name <b>Separator/Paster Paper Fibrous Glass</b>	1-4	65997-17-3	--	--	--

**NOTE: The contents of this product are toxic chemicals that are subject to the reporting requirements of section 302 and 313 of the Emergency Planning and Community Right-To-Know Act of 1986 (40CFR 355 and 372).**

**III. Physical Data**

Material is (at normal temperatures) <input checked="" type="checkbox"/> Solid <input checked="" type="checkbox"/> Liquid	Appearance and Odor <b>Battery Electrolyte (acid) is a clear to cloudy liquid with slight acidic odor. Acid saturated lead oxide is a dark reddish-brown to gray solid with slight acidic odor.</b>
Boiling Point (at 760 mm Hg) <b>Lead 1755°C Batt. Electrolyte (Acid) 110-112°C</b>	Melting Point <b>Lead 327.4°C</b>
Specific Gravity (H <sub>2</sub> O =1) <b>Battery Electrolyte (Acid) 1.210 - 1.300</b>	Vapor Pressure <input checked="" type="checkbox"/> (mm Hg at 20°C) <input checked="" type="checkbox"/> (PSIG) <b>Battery Electrolyte (Acid) 11.7</b>
Vapor Density (Air =1) <b>Battery Electrolyte (Acid) 3.4</b>	Solubility is H <sub>2</sub> O <b>Lead and Lead Dioxide are not soluble. Battery Electrolyte (acid) is 100% soluble in water.</b>
% Volatile By Weight <b>Not Determined</b>	Evaporation rate (Butyl Acetate = 1) <b>Not Determined</b>

	Title:	Date:	Rev:	Page:	File Name:
	<b>Material Safety Data Sheet for All Optima Batteries</b>	<b>10/17/11</b>	<b>M</b>	2 of 5	<b>MSDS battery</b>

#### IV. Health Hazard Information

**NOTE:** Under normal conditions of use, this product does not present a health hazard. The following information is provided for battery electrolyte (acid) and lead for exposure that may occur during battery production or container breakage or under extreme heat conditions such as fire

##### ROUTES AND METHODS OF ENTRY

###### Inhalation

**Acid mist may be generated during battery overcharging and may cause respiratory irritation. Seepage of acid from broken batteries may present inhalation exposure in a confined area.**

###### Skin Contact

**Battery electrolyte (acid) can cause severe irritation, burns and ulceration.**

###### Skin Absorption

**Skin absorption is not a significant route of entry.**

###### Eye Contact

**Battery electrolyte (acid) can cause severe irritation, burns, and cornea damage upon contact.**

###### Ingestion

**Hands contaminated by contact with internal components of a battery can cause ingestion of lead/lead compounds. Hands should be washed prior to eating, drinking, or smoking.**

##### SIGNS AND SYMPTOMS OF OVEREXPOSURE

###### Acute Effects

**Acute effects of overexposure to lead compounds are GI (gastrointestinal) upset, loss of appetite, diarrhea, constipation with cramping, difficulty in sleeping, and fatigue. Exposure and/or contact with battery electrolyte (acid) may lead to acute irritation of the skin, corneal damage of the eyes, and irritation of the mucous membranes of the eyes and upper respiratory system, including lungs.**

###### Chronic Effects

**Lead and its compounds may cause chronic anemia, damage to the kidneys and nervous system. Lead may also cause reproductive system damage and can affect developing fetuses in pregnant women. Battery electrolyte (acid) may lead to scarring of the cornea, chronic bronchitis, as well as erosion of tooth enamel in mouth breathers in repeated exposures.**

##### POTENTIAL TO CAUSE CANCER

The National Toxicological Program (NTP) and The International Agency for Research on Cancer (IARC) have classified "strong inorganic acid mist containing sulfuric acid" as a Category 1 carcinogen, a substance that is carcinogenic to humans. The ACGIH has classified "strong inorganic acid mist containing sulfuric acid" as an A2 carcinogen (suspected human carcinogen). These classifications do not apply to liquid forms of sulfuric acid or sulfuric acid solutions contained within a battery. Inorganic acid mist (sulfuric acid mist) is not generated under normal use of this product. Misuse of the product, such as overcharging, may result in the generation of sulfuric acid mist.

The NTP and the IARC have classified lead as an A3 carcinogen (animal carcinogen). While the agent is carcinogenic in experimental animals at relatively high doses, the agent is unlikely to cause cancer in humans except under uncommonly high levels of exposure. For further information, see the ACGIH's pamphlet, *1996 Threshold Limit Values and Biological Exposure Indices*.

##### EMERGENCY AND FIRST AID PROCEDURES

###### Inhalation

**Not expected for product under normal conditions of use. However, if acid vapor is released due to overcharging or abuse of the battery, remove exposed person to fresh air. If breathing is difficult, oxygen may be administered. If breathing has stopped, artificial respiration should be started immediately. Seek medical attention immediately.**

###### Skin

**Exposure not expected for product under normal conditions of use. However, if acid contacts skin, flush with water and mild soap. If irritation develops, seek medical attention immediately.**

###### Eyes

**Exposure not expected for product under normal conditions of use. However, if acid from broken battery case enters eyes, flush with water for at least 15 minutes. Seek medical attention immediately.**

###### Ingestion

**Not expected due to physical form of finished product. However, if internal components are ingested:  
Lead/Lead compounds: Consult a physician immediately for medical attention.  
Battery Electrolyte (Acid): Do not induce vomiting. Refer to a physician immediately for medical attention.**

##### MEDICAL CONDITIONS AGGRAVATED BY EXPOSURE

**Inorganic lead and its compounds can aggravate chronic forms of kidney, liver, and neurologic diseases. Contact of battery electrolyte (acid) with the skin may aggravate skin diseases such as eczema and contact dermatitis.**

	<b>Title:</b>	<b>Date:</b>	<b>Rev:</b>	<b>Page:</b>	<b>File Name:</b>
	<b>Material Safety Data Sheet for All Optima Batteries</b>	<b>10/17/11</b>	<b>M</b>	<b>3 of 5</b>	<b>MSDS battery</b>

#### V. Fire and Explosion Data

Flash Point (test method) <b>Hydrogen - 259°C</b>	Autoignition Temperature <b>Hydrogen 580°C</b>	Flammable Limits in Air, % by Vol. <b>Hydrogen LEL - 4.1 UEL - 74.2</b>
Extinguishing Media <b>Dry chemical, foam, or CO<sub>2</sub></b>		
Special Fire Fighting Procedures <b>Use positive pressure, self-contained breathing apparatus.</b>		
Unusual Fire and Explosion Hazard <b>The sealed lead acid battery is not considered flammable, but it will burn if involved in a fire. A short circuit can also result in a fire. Acid mists, smoke and decomposition products may be produced. Remove all ignition sources. Cool battery(s) to prevent rupture.</b>		

#### VI. Reactivity Data

Stability <input type="checkbox"/> Unstable <input checked="" type="checkbox"/> Stable	Conditions to Avoid <b>Sparks and other sources of ignition may ignite hydrogen gas.</b>
Incompatibility (materials to avoid) <b>Lead/lead compounds: Potassium, carbides, sulfides, peroxides, phosphorus, sulfur. Battery electrolyte (acid): Combustible materials, strong reducing agents, most metals, carbides, organic materials, chlorates, nitrates, picrates, and fulminates.</b>	
Hazardous Decomposition Products <b>Lead/Lead compounds: Oxides of lead and sulfur Battery electrolyte (acid): Hydrogen, sulfur dioxide, sulfur trioxide</b>	
Hazardous Polymerization <input type="checkbox"/> May Occur <input checked="" type="checkbox"/> Will Not Occur	Conditions to Avoid <b>High temperature. Battery electrolyte (acid) will react with water to produce heat. Can react with oxidizing or reducing agents.</b>

#### VII. Control Measures

Engineering Controls <b>Store sealed lead acid batteries at ambient temperature. Never recharge batteries in an unventilated, enclosed space. Do not subject product to open flame or fire. Avoid conditions that could cause arcing between terminals.</b>
Work Practices <b>Do not carry battery by terminals. Do not drop battery, puncture or attempt to open battery case. Avoid contact with the internal components of a battery.</b>
PERSONAL PROTECTIVE EQUIPMENT
Respiratory Protection <b>None required for normal handling of finished product.</b>
Eyes and Face <b>None required under for finished product under normal conditions of use. If necessary to handle broken product, chemical splash goggles are recommended.</b>
Hands, Arms, and Body <b>None required for normal handling of finished product. If necessary to handle broken product, Vinyl-coated, PVC, gauntlet-type gloves with rough finish are recommended..</b>
Other Special Clothing and Equipment <b>Safety footwear meeting the requirements of ANSI Z 41.1 – 1991 is recommended when it in necessary to handle the finished product.</b>

#### VIII. Safe Handling Precautions

Hygiene Practices <b>Wash hands thoroughly before eating, drinking, or smoking after handling batteries.</b>
Protective Measures to be Taken During Non-Routine Tasks, Including Equipment Maintenance <b>Do not carry battery by terminals. Do not drop battery, puncture or attempt to open battery case. Do not subject product to open flame or fire and avoid situations that could cause arcing between terminals.</b>



<b>Title:</b> Material Safety Data Sheet for All Optima Batteries	<b>Date:</b> 10/17/11	<b>Rev:</b> M	<b>Page:</b> 4 of 5	<b>File Name:</b> MSDS battery
---	--------------------------	------------------	------------------------	--------------------------------------

Protective Measures to be Taken if Material is Released or Spilled

**Remove combustible materials and all sources of ignition. Avoid contact with acid materials. Use soda ash, baking soda or lime to neutralize any acid that may be released.**

**If battery is broken, wear chemical goggles and acid-resistant gloves for handling the parts.**

**DO NOT RELEASE UNNEUTRALIZED ACID!**

Waste Disposal Method

**Battery Electrolyte (Acid): Neutralize as above for a spill, collect residue, and place in a drum or suitable container. Dispose of as a hazardous waste.**

**DO NOT FLUSH LEAD-CONTAMINATED ACID INTO SEWER.**

**Send spent or broken batteries to a lead recycling facility or smelter that follows applicable Federal, State and Local regulations for routine disposition of spent or damaged batteries. The distributor / user is responsible for assuring that these "spent" or "damaged" batteries are disposed of in an environmentally sound way in accordance with all regulations. OPTIMA batteries are 100% recyclable by any licensed reclamation operation..**



SUPPLEMENTAL INFORMATION

**Proposition 65 Warning (California) Proposition 65 Warning:** The state of California has listed lead as a material known to cause cancer or cause reproductive harm (July 9, 2004 California List of Chemicals Known to Cause Cancer or Reproductive Toxicity) Battery posts, terminals and related accessories contain lead and lead compounds. Batteries also contain other chemicals known to the State of California to cause cancer. Wash hands after handling.

**TSCA Registry:** Ingredients listed in the TSCA Registry are lead, lead compounds, and sulfuric acid.

**Transportation: Sealed Lead Acid Battery is not a DOT Hazardous Material.**

**Other: Per DOT, IATA, ICAO and IMDG rules and regulations, these batteries are exempt from "UN2800" classification as a result of successful completion of the following tests:**

- 1) Vibration Tests
- 2) Pressure Differential Tests
- 3) Case Rupturing Tests (no free liquids)

**US MILITARY NATIONAL STOCK NUMBER (NSN)**

Model Number	P/N	NSN
34/78	8004-003	6140-01-374-2243, 6140-01-457-4339
34	8002-002	6140-01-378-8232, 6140-01-493-1962
34R	8003-151	6140-01-475-9357
34VX	8008-158	6140-01-534-6466
25	8025-160	
35	8020-164	
75/25	8022-091	6140-01-475-9361
78	8078-109	
850/6 -1050 SLI	8010-044	6140-01-475-9414
DS46B24R	8171-767	
850/6 - 950 (DC)		
D51	8071-167	6140-01-523-6288
D51R	8073-167	6140-01-529-7226
D35	8040-218	
D75/25	8042-218	

	<b>Title:</b>	<b>Date:</b>	<b>Rev:</b>	<b>Page:</b>	<b>File Name:</b>
	<b>Material Safety Data Sheet for All Optima Batteries</b>	<b>10/17/11</b>	<b>M</b>	<b>5 of 5</b>	<b>MSDS battery</b>

D34	8012-021	6140-01-450-0141
D34/78	8014-045	6140-01-441-4272
D27F	8037-127	
D31T	8050-160	6140-01-457-5469
D31A	8051-160	6140-01-502-4973
34M	8006-006	6140-01-441-4280, 6140-01-526-2605
D34M	8016-103	6140-01-475-9355
D27M	8027-127	6140-01-589-0622
D31M	8052-161	6140-01-502-4405

**Disclaimer:** This information has been compiled from sources considered to be dependable and is, to the best of our knowledge and belief, accurate and reliable as of the date compiled. However, no representation, warranty (either express or implied) or guarantee is made to the accuracy, reliability or completeness of the information contained herein. This information relates to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. It is the user's responsibility to satisfy himself as to the suitability and completeness of this information for his own particular use. We do not accept liability for any loss or damage that may occur, whether direct, indirect, incidental or consequential, from use of this information.