

IE-KO-HAT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- Overpressure valve protects against overloading
- Cylinder head angled at 90°
- Angled head can be rotated through 360°
- Ergonomic handle springs back automatically
- The waste piece no longer becomes jammed thanks to triple splitting
- Hydraulic punch made of high-strength aluminium (approx. 40% weight saving)
- Service life greatly reduced when stainless steel sheets are used

General ordering data

Type	IE-KO-HAT
Order No.	1966810000
Version	Sheet holes
GTIN (EAN)	4032248659630
Qty.	1 pc(s).

IE-KO-HAT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Dimensions and weights

Width	290 mm	Width (inches)	11.417 inch
Height	120 mm	Height (inches)	4.724 inch
Depth	70 mm	Depth (inches)	2.756 inch
Weight	1.9 kg	Net weight	3,262 g

Cutting tools

Max. operating pressure	650 bar	Punching force	75 kN
Rectangular holes up to	36 x 112 mm; 2,0 mm F = 370 N/mm ²	Round holes from 1 to Ø 85 mm	2,0 mm F = 370 N/mm ²
Round holes from 2 to Ø 64 mm	3,0 mm F = 370 N/mm ²	Round holes from 3 to Ø 64 mm	2.5 mm F = 600 N/mm ²
Square holes up to	68 x 68 mm; 2.0 mm F = 370 N/mm ²		

Classifications

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000156
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	27-14-91-90	eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01	eClass 9.0	21-04-90-47
eClass 9.1	21-04-90-47		

Downloads

Brochure/Catalogue	CAT 9 IETH 15/16 EN CAT 3 HDC 17/18 EN CAT 6 TOOLS 15/16 EN CAT 5 ENCL 17/18 EN
--------------------	--

IE-KO-HAT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Example of use

