

Screwty M23**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The Screwty® attachment is suitable for customisable M23 round plug-in connectors and for overmoulded M23 round plug-in connectors, with an outside dimension of the knurled nut of 26.2 ± 0.3 mm. The tightening torque is 2-2.5 Nm.

General ordering data

Type	Screwty M23
Order No.	1981560000
Version	Tools, Bolting tool
GTIN (EAN)	4032248677702
Qty.	1 pc(s).

Screwty M23

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 23 g

Classifications

ETIM 3.0	EC001583	ETIM 4.0	EC001583
ETIM 5.0	EC001583	ETIM 6.0	EC000149
UNSPSC	30-21-18-01	eClass 6.2	27-14-92-06
eClass 7.1	27-14-92-06	eClass 8.1	27-14-92-06
eClass 9.0	21-04-50-03	eClass 9.1	21-01-90-90

Approvals

ROHS Conform

Downloads

Brochure/Catalogue [CAT 6 TOOLS 15/16 EN](#)
[CAT 8 SAI 15/16 EN](#)
[FL FIELDWIRING EN](#)