

**SAK Series
QL 20 DLI**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image

Similar to illustration

Signal wiring

Tailored and particularly compact: with our AIO initiator/actuator terminal blocks, you are relying on an application-optimised solution for signal wiring. We also offer you other terminal blocks featuring spring and screw connection technology for signal wiring.

General ordering data

Type	QL 20 DLI
Order No.	2083490000
Version	SAK Series, Cross-connection lug, for screwable cross-connection, No. of poles: 20
GTIN (EAN)	4008190248734
Qty.	1 pc(s).

Data sheet

SAK Series QL 20 DLI

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	120.9 mm	Width (inches)	4.76 inch
Height	4 mm	Height (inches)	0.157 inch
Depth	0.8 mm	Depth (inches)	0.031 inch
Net weight	2.25 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C		

Material data

Material	Copper	Surface finish	tinned
Colour	grey		

System specifications

Version	for screwable cross-connection
---------	--------------------------------

Additional technical data

Type of fixing	when screwed in
----------------	-----------------

Dimensions

Pitch in mm (P)	6.1 mm
-----------------	--------

Classifications

ETIM 3.0	EC000489	ETIM 4.0	EC000489
ETIM 5.0	EC000489	ETIM 6.0	EC000489
eClass 6.2	27-14-11-40	eClass 7.1	27-14-11-40
eClass 8.1	27-14-11-40	eClass 9.0	27-14-11-40
eClass 9.1	27-14-11-40		

Approvals

ROHS	Conform
------	---------