

PAC
PAC-UNIV-HE20-LCH-1M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Similar to illustration

Cable preconfeccionado cable plano según IEC-603/
DIN41651.

- Cable plano - cable plano
- Cable plano - punteras

General ordering data

Type	PAC-UNIV-HE20-LCH-1M
Order No.	7789306010
Version	Pre-assembled cable, PAC, Cable LiYY, 0.14 mm ²
GTIN (EAN)	8430243969062
Qty.	1 pc(s).

PAC

PAC-UNIV-HE20-LCH-1M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight 66 g

Temperatures

Operating temperature, max.	50 °C	Operating temperature, min.	-10 °C
Storage temperature, max.	60 °C	Storage temperature, min.	-10 °C
Operating temperature	-10...50 °C	Storage temperature	-10...60 °C

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

General Data

Connector PLC side	FLAT CABLE CONECTOR HE10 20P	Interface connector	FLAT CABLE CONECTOR HE10 20P
Number of poles, min.	20-pole	Outer diameter	8.6 ± 1 mm
Cable	Cable LiYY	Cable length	1 m
Material	PVC	Wire cross-section	0.14 mm ²

Electrical Data

Rated voltage (text)	≤ 60 Vdc ≤ 25 Vac	Permissible current strength per path, max.	1 A
Total current, max.	3 A	Resistance	≤ 150 mΩ/m
High voltage test	1 KV/1s		

Classifications

ETIM 3.0	EC000237	ETIM 5.0	EC000237
ETIM 6.0	EC000237	eClass 6.2	27-24-92-05
eClass 7.1	27-24-92-05	eClass 8.1	27-24-92-05
eClass 9.0	27-24-22-20	eClass 9.1	27-24-22-20

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue [CAT U_REMOTE 16/17 EN](#)