

BG GHDE 10P REG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The FieldPower® housings are highly robust and meet the highest UL flammability class 5 VA.

- The "TS 35 PT6" mounting rail module and PT6 contact unit are easy to snap on.
- Hinged seals allow pre-assembled plug cables to also be used.
- The high cover versions enable the device to be installed.

For cable seals consult accessories.

General ordering data

Available until	2012-09-15
Type	BG GHDE 10P REG
Order No.	8000007627
Version	Enclosures, IP54, Polycarbonate, GF 10
GTIN (EAN)	4050118116403
Qty.	1 pc(s).

BG GHDE 10P REG

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Net weight	715 g
------------	-------

Temperatures

Operating temperature, max.	40 °C	Operating temperature, min.	-40 °C
Operating temperature	-40 °C...40 °C	Storage temperature	

General information #96 connectors

UL 94 flammability rating	5VA
---------------------------	-----

General specifications

Halogen	No	Insulating material	Polycarbonate, GF 10
Protection degree	IP54	Silicone	No
Colour	black	UL 94 flammability rating	5VA
Lid attachment	Cross-head screws PZ2	Torque for lid screws	2 Nm

Technical data for equipment installation

Built-in power loss	See project help	Hinged cover insulating material	Polycarbonate
Hinged cover material cover	Transparent	Max. number of REG modules (18 mm) installable	6

Classifications

ETIM 5.0	EC000214	ETIM 6.0	EC000747
eClass 6.2	27-14-98-90	eClass 7.1	27-14-24-09
eClass 8.1	27-14-24-09	eClass 9.0	27-18-22-04
eClass 9.1	27-18-92-90		

Downloads

Approval/Certificate/Document of Conformity	FieldPower
---	----------------------------

BG GHDE 10P REG

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Drawings

