

Field bus components

FBCon PA CG 1way

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The FBCon Fieldbus distributor is available in the industry and EEx (ia) version. They are used for coupling from 1 to 8 field devices or sensors.

They are connected via spur lines. The connection to the spur line can be made with an M12 plug or directly via an EMC cable gland. Communication and device power feed are transferred by a common 2-wire line.

The distributors offer the following features respective of the version:

- Tension-clamp connection system
- Overvoltage protection for the main line
- Current limiter for each branch line
- EMC cable gland
- M12 plug-in connectors
- External earthing contact
- Interruption-free bus operation
- Industrial version
- Bus termination integrated (not EX)
- ATEX explosion-proof version
- Pressure-equalising element
- Protection degrees IP65, IP66, IP67
- Stainless steel versions
- PROFIBUS-PA compatible

General ordering data

Type	FBCon PA CG 1way
Order No.	8564090000
Version	Standard distributor, 1-way distributor, IP66
GTIN (EAN)	4032248235711
Qty.	1 pc(s).

Field bus components

FBCon PA CG 1way

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	64 mm	Length (inches)	2.52 inch
Width	58 mm	Width (inches)	2.283 inch
Height	37 mm	Height (inches)	1.457 inch
Net weight	262 g		

Temperatures

Operating temperature, max.	80 °C	Operating temperature, min.	-40 °C
Storage temperature, max.	80 °C	Storage temperature, min.	-40 °C
Operating temperature	-40 °C...80 °C	Ambient temperature	-40 °C...80 °C
Storage temperature	-40 °C...80 °C		

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Classifications

ETIM 3.0	EC000214	ETIM 4.0	EC001604
ETIM 5.0	EC001604	ETIM 6.0	EC001604
UNSPSC	26-12-16-03	eClass 5.1	27-25-02-01
eClass 6.2	27-24-26-08	eClass 7.1	27-24-26-08
eClass 8.1	27-24-26-08	eClass 9.0	27-24-26-08
eClass 9.1	27-24-26-08		

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 8 SAI 15/16 EN
User Documentation	assembly instruction german / english

Field bus components FBCon PA CG 1way

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

