

Field bus components

FBCon DP CG 1way

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The FBCon DP fieldbus distributors are used to couple 1 to 8 actuators, sensors or remote I/Os to a PROFIBUS network.

The branches (T-pieces) connect the individual bus components to the bus cable. The length of the branch cable depends on the transmission rate and should be as short as possible.

The total of all branch lengths for transmission rates up to 1.5 MBaud may not exceed 6.6 m.

The trunk line is run over EMC cable glands into an aluminium / stainless steel housing and connected using tension-clamp terminals.

The branch line to the device is connected using a B-coded M12 socket or an EMC cable gland.

Terminating resistors must be wired onto the start and end of the PROFIBUS-DP network. The Terminator modules can take care of this task.

The 24 V DC power supply is introduced via the right-hand cable gland. The housing features a pressure-compensation mechanism that counters the effects of climatic fluctuations.

The guidelines issued by the PROFIBUS user organisation must be observed during installation.

The distributors have the following characteristics:

- Tension-clamp connection system
- EMC cable gland
- M12 plug-in connectors

- External earthing contact
- Interruption-free bus operation
- Pressure-equalising element
- IP 66 protection class
- Stainless steel versions
- PROFIBUS-DP compatible

General ordering data

Type	FBCon DP CG 1way
Order No.	8564340000
Version	Standard distributor, IP66
GTIN (EAN)	4032248404698
Qty.	1 pc(s).

Field bus components

FBCon DP CG 1way

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	64 mm	Length (inches)	2.52 inch
Width	58 mm	Width (inches)	2.283 inch
Height	36 mm	Height (inches)	1.417 inch
Net weight	262 g		

Temperatures

Operating temperature, max.	80 °C	Operating temperature, min.	-40 °C
Storage temperature, max.	80 °C	Storage temperature, min.	-40 °C
Operating temperature	-40 °C...80 °C	Ambient temperature	-40 °C...80 °C
Storage temperature	-40 °C...80 °C		

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Connection data

Clamping range, min.	0.5 mm ²	Clamping range, max.	1.5 mm ²
----------------------	---------------------	----------------------	---------------------

Classifications

ETIM 3.0	EC000214	ETIM 4.0	EC001604
ETIM 5.0	EC001604	ETIM 6.0	EC001604
eClass 6.2	27-24-26-08	eClass 7.1	27-24-26-08
eClass 8.1	27-24-26-08	eClass 9.0	27-24-26-08
eClass 9.1	27-24-26-08		

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 8 SAI 15/16 EN
User Documentation	assembly instruction german / english

Field bus components

FBCon DP CG 1way

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

