

Field bus components FBCon SS CG 4way

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The FBCon Fieldbus distributor is available in the industry and EEx (ia) version. They are used for coupling from 1 to 8 field devices or sensors.

They are connected via spur lines. The connection to the spur line can be made with an M12 plug or directly via an EMC cable gland. Communication and device power feed are transferred by a common 2-wire line.

The distributors offer the following features respective of the version:

- Tension-clamp connection system
- Overvoltage protection for the main line
- Current limiter for each branch line
- EMC cable gland
- M12 plug-in connectors
- External earthing contact
- Interruption-free bus operation
- Industrial version
- Bus termination integrated (not EX)
- ATEX explosion-proof version
- Pressure-equalising element
- Protection degrees IP65, IP66, IP67
- Stainless steel versions
- PROFIBUS-PA compatible

General ordering data

Type	FBCon SS CG 4way
Order No.	8703450000
Version	Standard distributor, 4-way distributor, IP66
GTIN (EAN)	4032248398355
Qty.	1 pc(s).

Field bus components

FBCon SS CG 4way

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	125 mm	Length (inches)	4.921 inch
Width	80 mm	Width (inches)	3.15 inch
Height	36 mm	Height (inches)	1.417 inch
Net weight	866 g		

Temperatures

Operating temperature, max.	80 °C	Operating temperature, min.	-40 °C
Storage temperature, max.	80 °C	Storage temperature, min.	-40 °C
Operating temperature	-40 °C...80 °C	Ambient temperature	-40 °C...80 °C
Storage temperature	-40 °C...80 °C		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Classifications

ETIM 3.0	EC000214	ETIM 4.0	EC001604
ETIM 5.0	EC001604	ETIM 6.0	EC001604
UNSPSC	26-12-16-03	eClass 5.1	27-25-02-01
eClass 6.2	27-24-26-08	eClass 7.1	27-24-26-08
eClass 8.1	27-24-26-08	eClass 9.0	27-24-26-08
eClass 9.1	27-24-26-08		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 8 SAI 15/16 EN
User Documentation	assembly instruction german / english

Field bus components FBCon SS CG 4way

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

