

**Industrial Ethernet
IE-FM6Z2V00005MSD0SD0X**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Assembled IE cables, FO patch cable, multimode, SC duplex - SC duplex, orange, Core diameter 62.5 µm

General ordering data

Type	IE-FM6Z2V00005MSD0SD0X
Order No.	8876360050
Version	Pre-assembled patch cable, crossover, SC duplex IP 20, SC duplex IP 20, 62.5 µm, PVC, 5 m
GTIN (EAN)	4032248609710
Qty.	1 pc(s).

**Industrial Ethernet
IE-FM6Z2V00005MSD0SD0X**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Length	5 m	Length (inches)	0.197 inch
Net weight	98 g		

Temperatures

Operating temperature, max.	75 °C	Operating temperature, min.	-5 °C
Storage temperature, max.	75 °C	Storage temperature, min.	-25 °C
Operating temperature	-5 °C...75 °C	Storage temperature	-25 °C...75 °C
Installation temperature	-5 °C...50 °C		

Standards

Connector standard	IEC 61754-4
--------------------	-------------

Fibre-optic

Attenuation	≤ 3.2 dB/km at 850 nm, ≤ 0.9 dB/km at 1300 nm	Bandwidth	≥ 250 MHz*km at 850 nm, ≥ 600 MHz*km at 1300 nm
Fibre type	GOF, Multimode, OM1		

Cable structure

Core diameter	62.5 µm	Sheath diameter	3*6 mm
Cable layout	ZIPCORD	Standard designations	I-V(ZN)Y
Material sheath	PVC	Sheathing colour	orange

Mechanical and material properties of cable

Min. bending radius, once only	30 mm	Min. bending radius, repetitive	60 mm
--------------------------------	-------	---------------------------------	-------

plug

Connector left	SC duplex IP 20	Connector right	SC duplex IP 20
----------------	-----------------	-----------------	-----------------

Classifications

ETIM 3.0	EC000034	ETIM 4.0	EC000034
ETIM 5.0	EC000034	ETIM 6.0	EC002607
UNSPSC	30-21-18-01	eClass 5.1	27-06-18-03
eClass 6.2	27-06-18-03	eClass 7.1	27-06-18-03
eClass 8.1	27-06-18-03	eClass 9.0	27-06-10-03
eClass 9.1	27-06-10-03		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 9 IETH 15/16 EN FL FIELDWIRING EN PI PROFINET CABLING EN
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN

Creation date May 28, 2019 12:30:54 AM CEST

Catalogue status 23.05.2019 / We reserve the right to make technical changes.

Data sheet

**Industrial Ethernet
IE-FM6Z2V00005MSD0SD0X**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Detailed drawing

