

**Industrial Ethernet  
IE-FM5Z2V00010MST0ST0X**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



Assembled IE cables, FO patch cable, multimode, ST-ST,  
orange, Core diameter 50 µm

**General ordering data**

Type	IE-FM5Z2V00010MST0ST0X
Order No.	<a href="#">8876370100</a>
Version	Patch cable, ST IP 20, ST IP 20, 50 µm, PVC, 10 m
GTIN (EAN)	4032248609758
Qty.	1 pc(s).

**Industrial Ethernet  
IE-FM5Z2V00010MST0ST0X**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Length	10 m	Length (inches)	0.394 inch
Net weight	159 g		

**Temperatures**

Operating temperature, max.	75 °C	Operating temperature, min.	-5 °C
Storage temperature, max.	75 °C	Storage temperature, min.	-25 °C
Operating temperature	-5 °C...75 °C	Storage temperature	-25 °C...75 °C
Installation temperature	-5 °C...50 °C		

**Standards**

Connector standard	IEC 61754-2
--------------------	-------------

**Fibre-optic**

Attenuation	≤ 2.7 dB/km at 850 nm, ≤ 0.7 dB/km at 1300 nm	Bandwidth	≥ 600 MHz*km at 850 nm, ≥ 1200 MHz*km at 1300 nm
Fibre type	GOF, Multimode, OM2		

**Cable structure**

Core diameter	50 µm	Sheath diameter	3*6 mm
Cable layout	ZIPCORD	Standard designations	I-V(ZN)Y
Material sheath	PVC	Sheathing colour	orange

**Mechanical and material properties of cable**

Min. bending radius, once only	30 mm	Min. bending radius, repetitive	60 mm
--------------------------------	-------	---------------------------------	-------

**plug**

Connector left	ST IP 20	Connector right	ST IP 20
----------------	----------	-----------------	----------

**Classifications**

ETIM 3.0	EC000034	ETIM 4.0	EC000034
ETIM 5.0	EC000034	ETIM 6.0	EC002607
UNSPSC	30-21-18-01	eClass 5.1	27-06-18-03
eClass 6.2	27-06-18-03	eClass 7.1	27-06-18-03
eClass 8.1	27-06-18-03	eClass 9.0	27-06-10-03
eClass 9.1	27-06-10-03		

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Brochure/Catalogue	<a href="#">CAT 9 IETH 15/16 EN</a> <a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a>
User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>

Creation date May 28, 2019 12:31:00 AM CEST

**Data sheet**

**Industrial Ethernet  
IE-FM5Z2V00010MST0ST0X**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Detailed drawing**

---

---

