

**Industrial Ethernet
IE-XM-USB/USB-IP67****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



SnapIn plug-in connectors according to IEC 61076-3-106
ver.6 in plastic, with USB insert

General ordering data

Type	IE-XM-USB/USB-IP67
Order No.	8892670000
Version	Mounting flange, USB flange, Cat.6 (ISO/IEC 11801), IP67
GTIN (EAN)	4032248641123
Qty.	1 pc(s).

Industrial Ethernet IE-XM-USB/USB-IP67

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight	38 g
------------	------

Temperatures

Operating temperature, max.	85 °C	Operating temperature, min.	-20 °C
Operating temperature	-20 °C...85 °C	Storage temperature	
Installation temperature			

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

General Info

Connection 1	USB	Connection 2	USB
Description of article	USB flange	Colour	Light Grey
Housing main material	PA 66, UL 94: V-0	Category	Cat.6 (ISO/IEC 11801)
Type of mounting	Cabinet, Distribution box	Shielding	360°deg; shield contact
Protection degree	IP67	Plugging cycles	750

Classifications

ETIM 3.0	EC000211	ETIM 4.0	EC000211
ETIM 5.0	EC000211	ETIM 6.0	EC001121
UNSPSC	31-16-23-03	eClass 5.1	27-18-26-02
eClass 6.2	27-25-05-04	eClass 7.1	27-25-05-04
eClass 8.1	19-17-01-25	eClass 9.0	27-44-03-90
eClass 9.1	27-44-09-90		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	FL FIELDWIRING EN PI PROFINET CABLING EN
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN

Industrial Ethernet IE-XM-USB/USB-IP67

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Dimensioned drawing

