

Widerstandsbox 8x18K 3W

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The following products are available as functional components:

- Switch and button components in a sealed built-in EG2 enclosure
- Rectifier and fuse components in a sealed built-in EG2 enclosure
- Logic components with AND, NAND, OR and NOR operators
- Diode gates with up to 40 inputs in open design
- Components modules for the integration of electronic elements
- Serial interface converter, and AD / DA converter

General ordering data

Type	Widerstandsbox 8x18K 3W
Order No.	8943120000
GTIN (EAN)	4032248752713
Qty.	1 pc(s).

Widerstandsbox 8x18K 3W

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Dimensions and weights

Length	125 mm	Length (inches)	4.921 inch
Width	55.5 mm	Width (inches)	2.185 inch
Height	100 mm	Height (inches)	3.937 inch
Net weight	425 g		

Temperatures

Operating temperature, max.	70 °C	Operating temperature, min.	-25 °C
Storage temperature, max.	70 °C	Storage temperature, min.	-40 °C
Operating temperature	-25...70 °C	Ambient temperature	+70 °C
Storage temperature	-40...70 °C		

Connection data

Type of connection	Tension-clamp connection
--------------------	--------------------------

Insulation coordination (EN50178)

Pollution severity level	2
--------------------------	---

Connection field

Type of connection	Tension-clamp connection	Clamping range, min.	0.08 mm ²
Clamping range, max.	1 mm ²	Stripping length	7 mm

Classifications

ETIM 6.0	EC002024	eClass 6.2	25-13-90-90
eClass 7.1	25-13-90-90	eClass 8.1	25-13-90-90

Approvals

ROHS	Conform
------	---------