

**Accessories**  
**MEHA KP RT M-D-SPX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



- Flexible and solid wire with PVC, Teflon (PTFE) and silicone insulation
- No damage to the wire thanks to specially shaped blade
- No splicing of individual wires
- Blade inserts are easy to replace
- All inserts fit one housing
- Guide bars in the blade cassettes facilitate correct positioning of the wire in the tool

**General ordering data**

Type	MEHA KP RT M-D-SPX
Order No.	<a href="#">9003610000</a>
Version	Accessories, Set of cutters, Conductor with custom insulation, 7mm
GTIN (EAN)	4008190058272
Qty.	1 pc(s).

## Accessories MEHA KP RT M-D-SPX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Width	26 mm	Width (inches)	1.024 inch
Height	11.5 mm	Height (inches)	0.453 inch
Depth	16 mm	Depth (inches)	0.63 inch
Weight	13 g	Net weight	3.68 g

### Environmental Product Compliance

REACH SVHC Lead 7439-92-1

### Stripping tools

Cable type	Conductor with custom insulation	Colour	red
Max. conductor diameter	0.5 mm	Min. conductor diameter	0.3 mm
Stripping length, max.	7 mm	Stripping length, min.	3 mm

### Classifications

ETIM 3.0	EC001509	ETIM 4.0	EC000163
ETIM 5.0	EC000163	ETIM 6.0	EC001509
UNSPSC	23-17-16-04	eClass 5.1	21-04-91-14
eClass 6.2	21-04-91-14	eClass 7.1	21-04-91-14
eClass 8.1	21-04-91-14	eClass 9.0	21-04-92-37
eClass 9.1	21-04-48-90		

### Downloads

Brochure/Catalogue [CAT 6 TOOLS 15/16 EN](#)