

Accessories
MEHA KP GN M-D-SPX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



- Flexible and solid wire with PVC, Teflon (PTFE) and silicone insulation
- No damage to the wire thanks to specially shaped blade
- No splicing of individual wires
- Blade inserts are easy to replace
- All inserts fit one housing
- Guide bars in the blade cassettes facilitate correct positioning of the wire in the tool

General ordering data

Type	MEHA KP GN M-D-SPX
Order No.	9003620000
Version	Accessories, Set of cutters, Conductor with custom insulation, 7mm
GTIN (EAN)	4008190130527
Qty.	1 pc(s).

Accessories

MEHA KP GN M-D-SPX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	26 mm	Width (inches)	1.024 inch
Height	11.5 mm	Height (inches)	0.453 inch
Depth	16 mm	Depth (inches)	0.63 inch
Weight	8 g	Net weight	3.68 g

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Stripping tools

Cable type	Conductor with custom insulation	Colour	green
Max. conductor diameter	0.8 mm	Min. conductor diameter	0.55 mm
Stripping length, max.	7 mm	Stripping length, min.	3 mm

Classifications

ETIM 3.0	EC001509	ETIM 4.0	EC000163
ETIM 5.0	EC000163	ETIM 6.0	EC001509
UNSPSC	23-17-16-04	eClass 5.1	21-04-91-14
eClass 6.2	21-04-91-14	eClass 7.1	21-04-91-14
eClass 8.1	21-04-91-14	eClass 9.0	21-04-92-37
eClass 9.1	21-04-48-90		

Downloads

Brochure/Catalogue [CAT 6 TOOLS 15/16 EN](#)