

Tools
M-D-STRIPAX AWG 30+32

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



- Flexible and solid wire with PVC, Teflon (PTFE) and silicone insulation
- No damage to the wire thanks to specially shaped blade
- No splicing of individual wires
- Blade inserts are easy to replace
- All inserts fit one housing
- Guide bars in the blade cassettes facilitate correct positioning of the wire in the tool

General ordering data

Type	M-D-STRIPAX AWG 30+32
Order No.	9003700000
Version	Tools, Stripping and cutting tool, Conductor with custom insulation, 7mm
GTIN (EAN)	4008190064327
Qty.	1 pc(s).

Tools
M-D-STRIPAX AWG 30+32

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	82 mm	Width (inches)	3.228 inch
Height	135 mm	Height (inches)	5.315 inch
Depth	16 mm	Depth (inches)	0.63 inch
Weight	110 g	Net weight	96.28 g

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Stripping tools

Cable type	Conductor with custom insulation	Max. conductor diameter	0.3 mm
Min. conductor diameter	0.2 mm	Stripping length, max.	7 mm

Classifications

ETIM 3.0	EC000163	ETIM 4.0	EC000163
ETIM 5.0	EC000163	ETIM 6.0	EC002109
UNSPSC	23-17-16-04	eClass 5.1	21-04-03-01
eClass 6.2	21-04-38-90	eClass 7.1	21-04-38-90
eClass 8.1	21-04-38-90	eClass 9.0	21-04-37-06
eClass 9.1	21-04-37-06		

Downloads

Brochure/Catalogue [CAT 6 TOOLS 15/16 EN](#)

Data sheet

Tools
M-D-STRIPAX AWG 30+32

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Example of use

