

DMS 3
LG DMS PRO/ DMS 3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

General ordering data

Type	LG DMS PRO/ DMS 3
Order No.	9007460000
Version	Tools, 90 % bei 3x 500 V AC / > 91 % bei 3 x 400 V AC
GTIN (EAN)	4008190404970
Qty.	1 pc(s).

DMS 3 LG DMS PRO/ DMS 3

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Weight	600 g	Net weight	602.4 g
--------	-------	------------	---------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical data

Charging time	30 min
---------------	--------

Electric screwdriver

Battery voltage	3.6 V	Bit holder	1/4" DIN 3126 Form E6.3
Charger input	AC 220-240V~50-60Hz 30W	Charger output	DC 2.8...6V; 4.8A / 30W max.
Charging time	30 min	Idling speed	200 u. 600 min ⁻¹
Max. coupling torque	3 Nm	Rated voltage	3.6 V
Weight	600 g	Weight of charger	600 g

Classifications

ETIM 3.0	EC001395	ETIM 4.0	EC001395
ETIM 5.0	EC001395	ETIM 6.0	EC000359
UNSPSC	26-11-17-04	eClass 5.1	27-05-06-04
eClass 6.2	27-05-06-04	eClass 7.1	27-05-06-04
eClass 8.1	27-05-06-04	eClass 9.1	21-05-92-01

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
--------------------	--------------------------------------