

Screwdriver SDIS 1.2X6.5X150

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image



Similar to illustration

VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1.
SoftFinish grip

General ordering data

Type	SDIS 1.2X6.5X150
Order No.	9008420000
Version	Screwdriver, Blade width (B): 6.5 mm, Blade length: 150 mm, Blade thickness (A): 1.2 mm
GTIN (EAN)	4032248056385
Qty.	1 pc(s).

Data sheet

**Screwdriver
SDIS 1.2X6.5X150**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	270 mm	Width (inches)	10.63 inch
Weight	112 g	Net weight	104.1 g
Diameter	36 mm		

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Screwing tools

Blade length	150 mm	Blade thickness (A)	1.2 mm
Blade type	B	Blade width (B)	6.5 mm
Form	Slotted		

Classifications

ETIM 3.0	EC001395	ETIM 4.0	EC000174
ETIM 5.0	EC000174	ETIM 6.0	EC000158
UNSPSC	27-11-17-01	eClass 5.1	21-04-04-01
eClass 6.2	21-04-04-01	eClass 7.1	21-04-04-90
eClass 8.1	21-04-04-90	eClass 9.0	21-04-04-07
eClass 9.1	21-04-04-07		

Approvals

Approvals



Downloads

Approval/Certificate/Document of Conformity	Manufacturer's Declaration - Screwdrivers Declaration of the Manufacturer
Brochure/Catalogue	CAT 6 TOOLS 15/16 EN CAT 5 ENCL 17/18 EN CAT 2 PORTFOLIOGUIDE EN

Data sheet

**Screwdriver
SDIS 1.2X6.5X150**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

