

**Screwdriver  
SDIK PH2**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



VDE insulated crosshead screwdriver, for Phillips screws,  
SDIK PH DIN 7438, ISO 8764/2-PH, output to ISO 8764-  
PH, SoftFinish grip

**General ordering data**

Type	SDIK PH2
Order No.	<a href="#">9008580000</a>
Version	Screwdriver, Blade length: 100 mm
GTIN (EAN)	4032248056576
Qty.	1 pc(s).

**Data sheet**

**Screwdriver  
SDIK PH2**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	220 mm	Width (inches)	8.661 inch
Weight	104 g	Net weight	97 g
Diameter	36 mm		

**Environmental Product Compliance**

REACH SVHC Lead 7439-92-1

**Screwing tools**

Blade length	100 mm	Form	Philips
Size	2		

**Classifications**

ETIM 3.0	EC001395	ETIM 4.0	EC000174
ETIM 5.0	EC000174	ETIM 6.0	EC000144
UNSPSC	27-11-17-01	eClass 5.1	21-04-04-01
eClass 6.2	21-04-04-01	eClass 7.1	21-04-04-90
eClass 8.1	21-04-04-90	eClass 9.0	21-04-04-06
eClass 9.1	21-04-04-06		

**Approvals**

Approvals



**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">Manufacturer's Declaration - Screwdrivers</a>
Brochure/Catalogue	<a href="#">CAT 4.3 ELECTR 15/16 EN</a> <a href="#">CAT 6 TOOLS 15/16 EN</a> <a href="#">CAT 5 ENCL 17/18 EN</a>