

Pressing tool HTG 58/59

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Crimping tools for coaxial connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Type	HTG 58/59
Order No.	9012020000
Version	Pressing tool, Crimping tool for contacts, Hexagonal crimping
GTIN (EAN)	4008190018207
Qty.	1 pc(s).

Pressing tool HTG 58/59

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	200 mm	Width (inches)	7.874 inch
Weight	420 g	Net weight	418.7 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical data

Version	Mechanical, without interchangeable inserts
---------	---

Description of contact

Type of contact	Coaxial connector
-----------------	-------------------

tool data crimping

Crimping type/profile	Hexagonal crimping	Hexagon AF (A)	5.4 mm
Hexagon spanner width (A 2)	6.48 mm	Hexagon spanner width (A 3)	1.72 mm
Crimping station, width (B 1)	10 mm	Crimping station, width (B 2)	10 mm
Crimping station, width (B 3)	2.3 mm	Internal contact diameter (D)	2 mm

Classifications

ETIM 3.0	EC000524	ETIM 4.0	EC000524
ETIM 5.0	EC000168	ETIM 6.0	EC000168
UNSPSC	56-11-15-08	eClass 5.1	27-40-02-18
eClass 6.2	21-04-38-11	eClass 7.1	21-04-38-11
eClass 8.1	21-04-38-11	eClass 9.0	21-04-38-11
eClass 9.1	21-04-38-11		

Approvals

Approvals



Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
--------------------	--------------------------------------

Data sheet**Pressing tool
HTG 58/59**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings