Pressing tool
HTF 48

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Crimping tools for flat blade connectors and flat blade receptacles with open or rolled crimping claw

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With end stop for exact positioning of the contacts

General ordering data

Type	HTF 48
Order No.	9013080000
Version	Pressing tool, Crimping tool for contacts, 0.5mm², 2.5mm², B-Crimp
GTIN (EAN)	4008190113056
Qty.	1 pc(s).

Pressing tool
HTF 48

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	200 mm	Width (inches)	7.874 inch
Weight	438 g	Net weight	453.98 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1

Technical data

Version	Mechanical, without interchangeable inserts

Description of contact

Type of contact	F-plug / -sleeve	Crimping range, min.	0.5 mm²
Crimping range, max.	2.5 mm²	Plug width	4.8 mm

tool data crimping

Crimping profile 1, min.	0.5 mm²	Crimping type/profile	B-Crimp
Wire end ferrules cross-section, min.	0.5 mm²	Crimping profile 1, max.	1 mm²
Wire end ferrules cross-section, max.	2.5 mm²	Crimping profile 2, min.	1.5 mm²
Crimping profile 2, max.	2.5 mm²		

Classifications

ETIM 3.0	EC000168	ETIM 4.0	EC000168
ETIM 5.0	EC000168	ETIM 6.0	EC000168
UNSPSC	23-17-16-04	eClass 5.1	21-04-03-01
eClass 6.2	21-04-38-11	eClass 7.1	21-04-38-11
eClass 8.1	21-04-38-11	eClass 9.0	21-04-38-11
eClass 9.1	21-04-38-11		

Approvals

Approvals

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN

Pressing tool
HTF 48

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

