

Pressing tool HTF SUB-D

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Crimping tools for SUB-D contacts

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With end stop for exact positioning of the contacts

General ordering data

Type	HTF SUB-D
Order No.	9013260000
Version	Pressing tool, Crimping tool for contacts, 28AWG, 20AWG, FoderBcrimp
GTIN (EAN)	4008190056896
Qty.	1 pc(s).

Pressing tool HTF SUB-D

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	200 mm	Width (inches)	7.874 inch
Weight	438 g	Net weight	440.98 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical data

Version	Mechanical, without interchangeable inserts
---------	---

Description of contact

Type of contact	SUB-D	Crimping range, min.	28 AWG
Crimping range, max.	20 AWG		

tool data crimping

Crimping profile 1, min.	28 AWG	Crimping type/profile	FoderBcrimp
Crimping profile 1, max.	24 AWG	Crimping profile 2, min.	22 AWG
Crimping profile 2, max.	20 AWG		

Classifications

ETIM 3.0	EC000168	ETIM 4.0	EC000168
ETIM 5.0	EC000168	ETIM 6.0	EC000168
UNSPSC	23-17-16-04	eClass 5.1	21-04-03-01
eClass 6.2	21-04-38-11	eClass 7.1	21-04-38-11
eClass 8.1	21-04-38-11	eClass 9.0	21-04-38-11
eClass 9.1	21-04-38-11		

Approvals

Approvals



Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
--------------------	--------------------------------------

Pressing tool HTF SUB-D

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

