

**Pressing tool
HTF 63**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Crimping tools for flat blade connectors and flat blade receptacles with open or rolled crimping claw**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With end stop for exact positioning of the contacts

General ordering data

Type	HTF 63
Order No.	901340000
Version	Pressing tool, Crimping tool for contacts, 0.5mm ² , 2.5mm ² , B-Crimp
GTIN (EAN)	4008190056995
Qty.	1 pc(s).

Data sheet

**Pressing tool
HTF 63**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	200 mm	Width (inches)	7.874 inch
Weight	438 g	Net weight	438.2 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical data

Version	Mechanical, without interchangeable inserts
---------	---

Description of contact

Type of contact	F-plug / -sleeve	Crimping range, min.	0.5 mm ²
Crimping range, max.	2.5 mm ²	Plug width	6.3 mm

tool data crimping

Crimping profile 1, min.	0.5 mm ²	Crimping type/profile	B-Crimp
Crimping profile 1, max.	1 mm ²	Crimping profile 2, min.	1.5 mm ²
Crimping profile 2, max.	2.5 mm ²		

Classifications

ETIM 3.0	EC001396	ETIM 4.0	EC001396
ETIM 5.0	EC000168	ETIM 6.0	EC000168
UNSPSC	27-11-27-20	eClass 5.1	21-05-08-01
eClass 6.2	21-04-38-11	eClass 7.1	21-04-38-11
eClass 8.1	21-04-38-11	eClass 9.0	21-04-38-11
eClass 9.1	21-04-38-11		

Approvals

Approvals



Downloads

Approval/Certificate/Document of Conformity	Declaration of the Manufacturer
Brochure/Catalogue	CAT 6 TOOLS 15/16 EN CAT 2 PORTFOLIOGUIDE EN

Data sheet

**Pressing tool
HTF 63**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

