

**Pressing tool  
CTX CM 1.6/2.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Crimping tools for turned contacts**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.

**General ordering data**

|            |                                                                      |
|------------|----------------------------------------------------------------------|
| Type       | CTX CM 1.6/2.5                                                       |
| Order No.  | <a href="#">9018490000</a>                                           |
| Version    | Pressing tool, Crimping tool for contacts,<br>0.14mm², 4mm², W crimp |
| GTIN (EAN) | 4008190884598                                                        |
| Qty.       | 1 pc(s).                                                             |

## Pressing tool CTX CM 1.6/2.5

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

|        |        |                |            |
|--------|--------|----------------|------------|
| Width  | 250 mm | Width (inches) | 9.842 inch |
| Weight | 730 g  | Net weight     | 679.78 g   |

### Environmental Product Compliance

|            |                |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

### Technical data

|         |                                             |
|---------|---------------------------------------------|
| Version | Mechanical, without interchangeable inserts |
|---------|---------------------------------------------|

### Description of contact

|                      |                   |                      |                      |
|----------------------|-------------------|----------------------|----------------------|
| Type of contact      | Turned contacts   | Crimping range, min. | 0.14 mm <sup>2</sup> |
| Crimping range, max. | 4 mm <sup>2</sup> |                      |                      |

### tool data crimping

|                          |                      |                          |                      |
|--------------------------|----------------------|--------------------------|----------------------|
| Crimping profile 1, min. | 0.14 mm <sup>2</sup> | Crimping type/profile    | W crimp              |
| Crimping profile 1, max. | 0.5 mm <sup>2</sup>  | Crimping profile 2, min. | 0.75 mm <sup>2</sup> |
| Crimping profile 2, max. | 1 mm <sup>2</sup>    | Crimping profile 3, min. | 1.5 mm <sup>2</sup>  |
| Crimping profile 4, min. | 2.5 mm <sup>2</sup>  | Crimping profile 5       | 4 mm <sup>2</sup>    |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000385    | ETIM 4.0   | EC000385    |
| ETIM 5.0   | EC000168    | ETIM 6.0   | EC000168    |
| UNSPSC     | 23-17-16-04 | eClass 5.1 | 21-04-03-01 |
| eClass 6.2 | 21-04-38-11 | eClass 7.1 | 21-04-38-11 |
| eClass 8.1 | 21-04-38-11 | eClass 9.0 | 21-04-38-11 |
| eClass 9.1 | 21-04-38-11 |            |             |

### Approvals

Approvals



### Downloads

|                    |                                                                            |
|--------------------|----------------------------------------------------------------------------|
| Brochure/Catalogue | <a href="#">CAT 3 HDC 17/18 EN</a><br><a href="#">CAT 6 TOOLS 15/16 EN</a> |
| Engineering Data   | <a href="#">STEP</a>                                                       |

### Pressing tool CTX CM 1.6/2.5

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

