

Tools

POWERSTRIPPER 16,0

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- for automatic stripping of individual wires
- stripping of flexible wires according to DIN VDE 0295, Cl. 5
- Partial stripping of insulation, the isolation remains on wire end
- Change of tools not necessary
- Quick and easy setting for the proper cross-section
- Stripping length from 3 to 20 mm
- Min. conductor length: 22 mm + stripping length
- Electric drive

General ordering data

Type	POWERSTRIPPER 16,0
Order No.	9028480000
Version	Automatic machines, Automatic stripper
GTIN (EAN)	4032248064632
Qty.	1 pc(s).

Tools
POWERSTRIPPER 16,0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Width	190 mm	Width (inches)	7.48 inch
Height	230 mm	Height (inches)	9.055 inch
Depth	295 mm	Depth (inches)	11.614 inch
Weight	11 kg	Net weight	8,800 g

Technical data

Electrical connection	100-240 V / 50/65 Hz
-----------------------	----------------------

Automatic stripping

Conductor length, min.	22 mm + stripping length	Connection values	46 VA
Drive	electrical	Electrical connection	100-240 V / 50/65 Hz
Pull-off length	3-20 mm	Pulse time	approx. 1.5 s
Stripping range	2.5 - 16 mm ² (~AWG 14-6)		

Classifications

ETIM 3.0	EC000163	ETIM 4.0	EC000163
ETIM 5.0	EC000163	ETIM 6.0	EC002778
UNSPSC	27-11-15-10	eClass 5.1	17-13-01-02
eClass 6.2	17-13-01-02	eClass 7.1	17-13-01-02
eClass 8.1	17-13-01-02	eClass 9.0	17-13-01-01
eClass 9.1	17-13-01-02		

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	WSCAD
User Documentation	Manual

Data sheet

Tools
POWERSTRIPPER 16,0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

