

CRIMPFIX L**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

Type	CRIMPFIX L
Order No.	9028530000
Version	Automatic machines, Automatic stripper and crimper
GTIN (EAN)	4008190942670
Qty.	1 pc(s).

CRIMPFIX L

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Dimensions and weights

Width	390 mm	Width (inches)	15.354 inch
Height	460 mm	Height (inches)	18.11 inch
Depth	330 mm	Depth (inches)	12.992 inch
Weight	31 kg	Net weight	34,000 g

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Technical data

Electrical connection 100-240 V / 50/65 Hz

PW65 maintenance - automatic stripping/crimping

Compressed-air connection	5 bar	Consumables	loose wire-end ferrules, with plastic collar
Crimping length	8 mm	Drive	Electropneumatic
Electrical connection	100-240 V / 50/65 Hz	Length of wire-end ferrule	14 mm
Pulse time	approx. 1 s	Stripping range	0.5 - 2.5 mm ²
Wire end ferrules cross-section, max.	2.5 mm ²	Wire end ferrules cross-section, min.	0.5 mm ²

Classifications

ETIM 3.0	EC000163	ETIM 4.0	EC000163
ETIM 5.0	EC000163	ETIM 6.0	EC002778
UNSPSC	27-11-15-10	eClass 5.1	17-13-01-01
eClass 6.2	17-13-01-01	eClass 7.1	17-13-01-01
eClass 8.1	17-13-01-01	eClass 9.0	17-13-01-01
eClass 9.1	17-13-01-01		

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue [CAT 6 TOOLS 15/16 EN](#)
 User Documentation [Manual](#)