

RZ 160**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



**up to 1000 V (AC) and 1500 V (DC)
protective insulation acc. to IEC 900. DIN EN 60900**

- drop-forged from high-quality special tool steels
- safety handle with ergonomic and non-slip TPE VDE sleeve
- Made from shockproof, heat-and cold-resistant, non-flammable, cadmium-free TPE (thermoplastic elastomer)
- Elastic grip zone and hard core
- Highly-polished surface
- nickel-chromium electro-galvanised coating protects against corrosion

General ordering data

Type	RZ 160
Order No.	9046360000
Version	VDE-insulated round-nose pliers with long jaws
GTIN (EAN)	4032248357666
Qty.	1 pc(s).

RZ 160

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	160 mm	Width (inches)	6.299 inch
Weight	153 g	Net weight	132.2 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Classifications

ETIM 3.0	EC000834	ETIM 4.0	EC000834
ETIM 5.0	EC000834	UNSPSC	23-17-16-04
eClass 5.1	21-04-03-01	eClass 6.2	21-04-38-90
eClass 7.1	21-04-38-90	eClass 8.1	21-04-38-90

Approvals

Approvals



Downloads

Approval/Certificate/Document of Conformity	Manufacturer's Declaration - Pliers
Brochure/Catalogue	CAT 6 TOOLS 15/16 EN

Data sheet

RZ 160

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

