

ERAN MULTI-STRIPAX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- For flexible and solid conductors with special insulating materials
- High-quality stripping for industrial applications (complies with aircraft industry requirements)
- Specially shaped blades enable stripping of special types of insulation and conductor configurations
- Stripping length adjustable via end stop
- Very versatile thanks to interchangeable stripping units
- Stripping results reproduced accurately over and over again
- No damage to the conductor
- A long-lasting, reliable tool thanks to its sturdy design
- Integrated cutting function

General ordering data

Type	ERAN MULTI-STRIPAX
Order No.	9203100000
Version	Spare stop set
GTIN (EAN)	4032248538102
Qty.	1 pc(s).

ERAN MULTI-STRIPAX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	250 mm	Width (inches)	9.842 inch
Height	85 mm	Height (inches)	3.346 inch
Weight	250 g	Net weight	11.88 g

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Stripping tools

max. cutting capacity, fine-strand	6 mm ²	max. cutting capacity, ribbon	10,2 mm x 4 mm
max. cutting capacity, solid	2.5 mm ²		

Classifications

ETIM 3.0	EC000163	ETIM 4.0	EC000163
ETIM 5.0	EC000163	ETIM 6.0	EC000149
UNSPSC	30-21-18-01	eClass 6.2	21-05-92-90
eClass 7.1	21-05-92-90	eClass 8.1	21-05-92-90
eClass 9.0	21-04-50-03	eClass 9.1	21-04-90-90

Downloads

Brochure/Catalogue [CAT 9 IETH 15/16 EN](#)
[CAT 6 TOOLS 15/16 EN](#)
[CAT 8 SAI 15/16 EN](#)