

KOBBS 19X75**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Weidmüller punching tools should be your first choice for making cut-outs in your electrical cabinets!

- PG cable glands
- M cable glands
- Special cable glands

General ordering data

Type	KOBBS 19X75
Order No.	9204780000
Version	Sheet holes
GTIN (EAN)	4032248693146
Qty.	1 pc(s).

KOBBS 19X75

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data**Dimensions and weights**

Height	75 mm	Height (inches)	2.953 inch
Weight	280 g	Net weight	292 g
Diameter	19 mm		

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Classifications

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000149
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	21-04-91-14	eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01	eClass 9.0	21-04-50-03
eClass 9.1	21-01-92-90		

Downloads

Brochure/Catalogue [CAT 6 TOOLS 15/16 EN](#)
[CAT 5 ENCL 17/18 EN](#)