

**Testing tools**  
**LSP 4L**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



The main function of the voltage tester is to establish if voltage is present. A 2-pole voltage tester is the only approved testing instrument that fulfils the requirements of work protection regulations.

- with LCD-Display
- acc. to VDE standard,
- high peak voltage strength
- the right tester for every application

**General ordering data**

Type	LSP 4L
Order No.	<a href="#">9205050000</a>
Version	2-pole voltage tester type 1153
GTIN (EAN)	4032248697311
Qty.	1 pc(s).

**Data sheet**

**Testing tools  
LSP 4L**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	231 mm	Width (inches)	9.094 inch
Height	37 mm	Height (inches)	1.457 inch
Depth	48 mm	Depth (inches)	1.89 inch
Weight	170 g	Net weight	173.5 g

**Environmental Product Compliance**

REACH SVHC Lead 7439-92-1

**Measuring and testing devices**

AC voltage measuring range	12-690 V	Continuity test	Yes
DC voltage measuring range	690 V	Display	digital
Frequency range, max.	500 Hz	Frequency range, min.	0 Hz
Measuring range category	CAT III – 690V/CAT IV – 600V	Peak voltage resistance	8 kV
Protection degree	IP65	Rated voltage, max.	690 V AC/DC
Rated voltage, min.	12 V AC/DC	Tested and approved according to	EN/IEC 61243-3 :2010-10 (VDE 0682 Part 401)
Working temperature, max.	45 °C	Working temperature, min.	-15 °C

**Classifications**

ETIM 3.0	EC000494	ETIM 4.0	EC000494
ETIM 5.0	EC000494	ETIM 6.0	EC000494
UNSPSC	41-11-36-37	eClass 5.1	27-20-03-08
eClass 6.2	27-20-03-08	eClass 7.1	27-20-03-08
eClass 8.1	27-20-03-08	eClass 9.0	27-20-03-08
eClass 9.1	27-20-03-08		

**Approvals**

Approvals



ROHS Conform

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">9205050000_DECLARATION_OF_CONFORMITY.pdf</a>
Brochure/Catalogue	<a href="#">CAT 6 TOOLS 15/16 EN</a>