

Testing tools
LAN USB TESTER

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The fully insulated plastic housings of our continuity testers are shockproof and unbreakable, making these instruments ideal for daily use, even in tough conditions. The integrated torch makes it easier to locate defective cables quickly and safely. The results of the continuity test can be conveyed visually and acoustically.

General ordering data

Type	LAN USB TESTER
Order No.	920540000
Version	Continuity tester for data cables
GTIN (EAN)	4032248732128
Qty.	1 pc(s).

Testing tools LAN USB TESTER

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	135 mm	Width (inches)	5.315 inch
Height	27 mm	Height (inches)	1.063 inch
Depth	65 mm	Depth (inches)	2.559 inch
Weight	174 g	Net weight	355 g

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Measuring and testing devices

Display	LED	Protection degree	IP44
Remote box dimensions	65 x 28 x 27 mm	Remote box weight	30 g
Supply	9V battery	Testable cable length, max.	1,000 m
Tested and approved according to	EN/ IEC 61010	Type of connection	RJ45, USB A, USB B

Classifications

ETIM 3.0	EC000495	ETIM 4.0	EC000069
ETIM 5.0	EC000069	ETIM 6.0	EC002080
UNSPSC	41-11-36-37	eClass 5.1	27-20-11-06
eClass 6.2	27-20-03-01	eClass 7.1	27-20-03-01
eClass 8.1	27-20-03-01	eClass 9.0	27-20-11-08
eClass 9.1	27-20-03-90		

Approvals

ROHS Conform

Downloads

Brochure/Catalogue [CAT 9 IETH 15/16 EN](#)
[CAT 6 TOOLS 15/16 EN](#)

Data sheet

**Testing tools
LAN USB TESTER**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Example of use

