

## Klippon POK (polyester empty enclosure) POK MOPL 0808

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



### Mounting plates for Klippon® POK enclosures

Mounting plates made out of 2 mm sheet steel, for longitudinal and transverse mounting of DIN rails, or for mounting components directly onto the mounting plate.

### General ordering data

Type	POK MOPL 0808
Order No.	<a href="#">9510570000</a>
Version	Klippon POK (polyester empty enclosure), Mounting plate, Height: 64 mm, Width: 69 mm, Depth: 1.5 mm, Material: Sheet steel, galvanized, galvanized, silver
GTIN (EAN)	4032248415274
Qty.	1 pc(s).

**Klippon POK (polyester empty enclosure)  
POK MOPL 0808**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Width	69 mm	Width (inches)	2.717 inch
Height	64 mm	Height (inches)	2.52 inch
Depth	1.5 mm	Depth (inches)	0.059 inch
Mounting dimension - width	59 mm	Net weight	11 g

**General information**

Material thickness	1.5 mm	Material	Sheet steel, galvanized
Surface finish	galvanized		

**General information on accessories**

Material	Sheet steel, galvanized	Material thickness	1.5 mm
Mounting dimension - width	59 mm	Surface finish	galvanized
Type of fixing	when screwed in		

**Classifications**

ETIM 3.0	EC000318	ETIM 4.0	EC002620
ETIM 5.0	EC002620	ETIM 6.0	EC000213
UNSPSC	31-16-23-03	eClass 5.1	27-18-92-07
eClass 6.2	27-18-92-61	eClass 7.1	27-18-92-61
eClass 8.1	27-18-92-61	eClass 9.0	27-40-06-39
eClass 9.1	27-18-92-90		

**Approvals**

Approvals



ROHS Conform

**Downloads**

Brochure/Catalogue	<a href="#">CAT 5 ENCL 17/18 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD</a>
Engineering Data	<a href="#">STEP</a>