

**Klippon POK (polyester empty enclosure)
POK MOPL 1222**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Mounting plates for Klippon® POK enclosures**

Mounting plates made out of 2 mm sheet steel, for longitudinal and transverse mounting of DIN rails, or for mounting components directly onto the mounting plate.

General ordering data

Type	POK MOPL 1222
Order No.	9510600000
Version	Klippon POK (polyester empty enclosure), Mounting plate, Height: 107 mm, Width: 207 mm, Depth: 1.5 mm, Material: Sheet steel, galvanized, Miscellaneous, silver
GTIN (EAN)	4008190498238
Qty.	1 pc(s).

Klippon POK (polyester empty enclosure) POK MOPL 1222

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	207 mm	Width (inches)	8.15 inch
Height	107 mm	Height (inches)	4.213 inch
Depth	1.5 mm	Depth (inches)	0.059 inch
Mounting dimension - width	193 mm	Mounting dimension - height	52 mm
Net weight	237 g		

General information

Material thickness	1.5 mm	Material	Sheet steel, galvanized
Surface finish	Miscellaneous		

General information on accessories

Material	Sheet steel, galvanized	Material thickness	1.5 mm
Mounting dimension - height	52 mm	Mounting dimension - width	193 mm
Surface finish	Miscellaneous	Type of fixing	when screwed in

Classifications

ETIM 3.0	EC000318	ETIM 4.0	EC002620
ETIM 5.0	EC002620	ETIM 6.0	EC000213
UNSPSC	31-16-23-03	eClass 5.1	27-18-92-07
eClass 6.2	27-18-92-61	eClass 7.1	27-18-92-61
eClass 8.1	27-18-92-61	eClass 9.0	27-40-06-39
eClass 9.1	27-18-92-90		

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP