

Klippon POK (polyester empty enclosure) POK MOPL 2540

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Mounting plates for Klippon® POK enclosures

Mounting plates made out of 2 mm sheet steel, for longitudinal and transverse mounting of DIN rails, or for mounting components directly onto the mounting plate.

General ordering data

Type	POK MOPL 2540
Order No.	9510650000
Version	Klippon POK (polyester empty enclosure), Mounting plate, Height: 234 mm, Width: 384 mm, Depth: 1.5 mm, Material: Sheet steel, galvanized, Miscellaneous, silver
GTIN (EAN)	4032248415298
Qty.	1 pc(s).

**Klippon POK (polyester empty enclosure)
POK MOPL 2540**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Width	384 mm	Width (inches)	15.118 inch
Height	234 mm	Height (inches)	9.213 inch
Depth	1.5 mm	Depth (inches)	0.059 inch
Mounting dimension - width	372 mm	Mounting dimension - height	100 mm
Net weight	1,046 g		

General information

Material thickness	1.5 mm	Material	Sheet steel, galvanized
Surface finish	Miscellaneous		

General information on accessories

Material	Sheet steel, galvanized	Material thickness	1.5 mm
Mounting dimension - height	100 mm	Mounting dimension - width	372 mm
Surface finish	Miscellaneous	Type of fixing	when screwed in

Classifications

ETIM 3.0	EC000318	ETIM 4.0	EC002620
ETIM 5.0	EC002620	ETIM 6.0	EC000213
UNSPSC	31-16-23-03	eClass 5.1	27-18-92-07
eClass 6.2	27-18-92-61	eClass 7.1	27-18-92-61
eClass 8.1	27-18-92-61	eClass 9.0	27-40-06-39
eClass 9.1	27-18-92-90		

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP