

**Klippon POK (polyester empty enclosure)
POK MOPL 2560**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Mounting plates for Klippon® POK enclosures**

Mounting plates made out of 2 mm sheet steel, for longitudinal and transverse mounting of DIN rails, or for mounting components directly onto the mounting plate.

General ordering data

Type	POK MOPL 2560
Order No.	9510660000
Version	Klippon POK (polyester empty enclosure), Mounting plate, Height: 233 mm, Width: 583 mm, Depth: 1.5 mm, Material: Sheet steel, galvanized, Miscellaneous, silver
GTIN (EAN)	4008190498306
Qty.	1 pc(s).

**Klippon POK (polyester empty enclosure)
POK MOPL 2560**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Width	583 mm	Width (inches)	22.953 inch
Height	233 mm	Height (inches)	9.173 inch
Depth	1.5 mm	Depth (inches)	0.059 inch
Mounting dimension - width	573 mm	Mounting dimension - height	100 mm
Net weight	1,308.4 g		

General information

Material thickness	1.5 mm	Material	Sheet steel, galvanized
Surface finish	Miscellaneous		

General information on accessories

Material	Sheet steel, galvanized	Material thickness	1.5 mm
Mounting dimension - height	100 mm	Mounting dimension - width	573 mm
Surface finish	Miscellaneous	Type of fixing	when screwed in

Classifications

ETIM 3.0	EC000318	ETIM 4.0	EC002620
ETIM 5.0	EC002620	ETIM 6.0	EC000213
UNSPSC	31-16-23-03	eClass 5.1	27-18-92-07
eClass 6.2	27-18-92-61	eClass 7.1	27-18-92-61
eClass 8.1	27-18-92-61	eClass 9.0	27-40-06-39
eClass 9.1	27-18-92-90		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP