

STRIPPER COAX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- For fast and accurate stripping of cables for damp areas ranging from 8 - 13 mm diameter, e.g. NYM cable, 3 x 1.5 mm² to 5 x 2.5 mm²
- No need to set cutting depth
- Ideal for working in junction and distribution boxes

General ordering data

| | |
|------------|--|
| Type | STRIPPER COAX |
| Order No. | 9918030000 |
| Version | Sheathing strippers, Coaxial & round data cables |
| GTIN (EAN) | 4032248359141 |
| Qty. | 1 pc(s). |

STRIPPER COAX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|--------|---------|-----------------|------------|
| Width | 97 mm | Width (inches) | 3.819 inch |
| Height | 20.5 mm | Height (inches) | 0.807 inch |
| Depth | 18.5 mm | Depth (inches) | 0.728 inch |
| Weight | 22 g | Net weight | 39 g |

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Stripping tools

| | | | |
|-------------------------|-----------------------------|-------------------------|--------|
| Cable type | Coaxial & round data cables | Max. conductor diameter | 7.5 mm |
| Min. conductor diameter | 4.8 mm | | |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC000163 | ETIM 4.0 | EC000163 |
| ETIM 5.0 | EC000163 | ETIM 6.0 | EC000163 |
| UNSPSC | 27-11-15-03 | eClass 5.1 | 21-04-06-02 |
| eClass 6.2 | 21-04-06-02 | eClass 7.1 | 21-04-91-03 |
| eClass 8.1 | 21-04-91-03 | eClass 9.0 | 21-04-90-90 |
| eClass 9.1 | 21-04-37-06 | | |

Approvals

Approvals



Downloads

Brochure/Catalogue [CAT 6 TOOLS 15/16 EN](#)

STRIPPER COAX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

