

STRIPPER ROUND TOP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- For fast and accurate stripping of cables for damp areas ranging from 8 - 13 mm diameter, e.g. NYM cable, 3 x 1.5 mm² to 5 x 2.5 mm²
- No need to set cutting depth
- Ideal for working in junction and distribution boxes

General ordering data

Type	STRIPPER ROUND TOP
Order No.	9918050000
Version	Sheathing strippers, Flexible and solid conductors with PVC insulation, 4mm ²
GTIN (EAN)	4032248359165
Qty.	1 pc(s).

STRIPPER ROUND TOP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Width	125 mm	Width (inches)	4.921 inch
Height	35 mm	Height (inches)	1.378 inch
Depth	25 mm	Depth (inches)	0.984 inch
Weight	50 g	Net weight	46.2 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Stripping tools

Cable type	Flexible and solid conductors with PVC insulation	Conductor cross-section, max.	4 mm ²
Conductor cross-section, min.	0.2 mm ²	Max. conductor diameter	13 mm
Min. conductor diameter	8 mm	Stripping range, min.	0.25 mm ²

Classifications

ETIM 3.0	EC000163	ETIM 4.0	EC000163
ETIM 5.0	EC000163	ETIM 6.0	EC000163
UNSPSC	27-11-15-03	eClass 5.1	21-04-06-02
eClass 6.2	21-04-06-02	eClass 7.1	21-04-91-03
eClass 8.1	21-04-91-03	eClass 9.0	21-04-90-90
eClass 9.1	21-04-37-06		

Approvals

Approvals

**Downloads**

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
--------------------	--------------------------------------

STRIPPER ROUND TOP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

