

DMS MANUELL 2,0-7,0

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



If you demand effective and exact work, it is essential to use the precise torque. This also guarantees high repetition accuracy.

This is the perfect job for the new Weidmüller torque screwdriver with the ergonomic grip and the unique interchangeable bit system.

- Compact and especially light design
- Torque set with special tool (supplied); an unintended, incorrect setting is ruled out.
- Ergonomic handle sizes matched to the torque range.
- Tools subjected to routine testing and provided with an ID number; 100% quality control with verification and product reference.
- Clicking sound upon reaching the set torque, clearly audible and noticeable, no unnecessary tightening.
- Interchangeable blades made from high-quality wear-resistant tool steel.
- All tools fulfil the accuracy requirements of: EN ISO 6798, BS EN 26789, ASME B107.14M
- Trigger accuracy +/- 6% of the set scale value.

General ordering data

Type	DMS MANUELL 2,0-7,0
Order No.	9918380000
Version	Tools, Torque screwdriver
GTIN (EAN)	4032248388349
Qty.	1 pc(s).

DMS MANUELL 2,0-7,0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Width	240 mm	Width (inches)	9.449 inch
Weight	538 g	Net weight	530 g

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Classifications

ETIM 3.0	EC001395	ETIM 4.0	EC000158
ETIM 5.0	EC000158	ETIM 6.0	EC000149
UNSPSC	27-11-17-01	eClass 5.1	21-04-04-01
eClass 6.2	21-04-04-01	eClass 7.1	21-04-04-90
eClass 8.1	21-04-04-90	eClass 9.0	21-04-04-07
eClass 9.1	21-04-04-90		

Approvals

Approvals

**Downloads**

Brochure/Catalogue [CAT 3 HDC 17/18 EN](#)
[CAT 6 TOOLS 15/16 EN](#)
[CAT 5 ENCL 17/18 EN](#)