

WK S 0,4X2,5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Interchangeable bits for torque screwdriver**

Drive output acc. to DIN 5264, ISO 2380/1

General ordering data

Type	WK S 0,4X2,5
Order No.	9918520000
Version	Screwdriver insert, Blade width (B): 2.5 mm, 175 mm, Blade thickness (A): 0.4 mm
GTIN (EAN)	4032248388882
Qty.	1 pc(s).

WK S 0,4X2,5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Width	175 mm	Width (inches)	6.89 inch
Height	4 mm	Height (inches)	0.157 inch
Depth	4 mm	Depth (inches)	0.157 inch
Weight	24 g	Net weight	21 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Screwing tools

Blade length	175 mm	Blade thickness (A)	0.4 mm
Blade width (B)	2.5 mm	Form	Slotted

Classifications

ETIM 3.0	EC001395	ETIM 4.0	EC001395
ETIM 5.0	EC001395	ETIM 6.0	EC002116
UNSPSC	27-11-28-14	eClass 5.1	21-04-04-02
eClass 6.2	21-04-92-21	eClass 7.1	21-04-04-90
eClass 8.1	21-04-04-90	eClass 9.1	21-04-04-90

Approvals

Approvals

**Downloads**

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 6 TOOLS 15/16 EN CAT 5 ENCL 17/18 EN
--------------------	---