

**WK K PH2****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Interchangeable bits for torque screwdriver**

Drive output acc. to DIN 5260-PH, ISO 8764/1-PH

**General ordering data**

Type	WK K PH2
Order No.	<a href="#">9918590000</a>
Version	Screwdriver insert, 175 mm, 2
GTIN (EAN)	4032248388967
Qty.	1 pc(s).

**WK K PH2**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	175 mm	Width (inches)	6.89 inch
Height	4 mm	Height (inches)	0.157 inch
Depth	4 mm	Depth (inches)	0.157 inch
Weight	22 g	Net weight	22 g

**Environmental Product Compliance**

REACH SVHC Lead 7439-92-1

**Screwing tools**

Blade length	175 mm	Blade size, crosshead	2
Form	Crosshead	Size	2

**Classifications**

ETIM 3.0	EC001395	ETIM 4.0	EC001395
ETIM 5.0	EC001395	ETIM 6.0	EC002115
UNSPSC	27-11-28-14	eClass 5.1	21-04-04-02
eClass 6.2	21-04-92-21	eClass 7.1	21-04-04-90
eClass 8.1	21-04-04-90	eClass 9.1	21-04-04-90

**Approvals**

Approvals



**Downloads**

Brochure/Catalogue [CAT 3 HDC 17/18 EN](#)  
[CAT 6 TOOLS 15/16 EN](#)  
[CAT 5 ENCL 17/18 EN](#)