

TSLD 5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Cutting and punching tool for terminal rails and profiled rails**

- TS 15/5.5 mm according to EN 50045 (s= 1.0 mm)
- TS 32 mm to EN 50035 (s= 1.5 mm)
- Copper grounding rail 10 mm x 3 mm
- TS 35/7.5 mm (s=1.0 mm) and TS 35/15 mm (s=1.5 mm) according to EN 50022

Punching

Longitudinal and cross perforations (long hole 12 x 6.4 mm)

(s = material thickness of mounting rail)

Note on TSLD C:

G profile is replaced by C profile.

C profile is individually adapted according to template.

General ordering data

Type	TSLD 5
Order No.	9918700000
Version	Tools, Mounting rail cutter
GTIN (EAN)	4032248395620
Qty.	1 pc(s).

TSLD 5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	270 mm	Width (inches)	10.63 inch
Height	205 mm	Height (inches)	8.071 inch
Depth	200 mm	Depth (inches)	7.874 inch
Weight	19,000 g	Net weight	17,634 g

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Classifications

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000142
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	21-04-90-90	eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01	eClass 9.0	21-04-47-01
eClass 9.1	21-04-37-06		

Downloads

Brochure/Catalogue [CAT 6 TOOLS 15/16 EN](#)