

SAK Series
STB 14/D5/2.3/M3 SAK2.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The SAKR disconnect terminals are available already fitted with sockets (see disconnect terminals). The sockets are equipped with a slit so that they can be actuated with a screwdriver. Weidmüller can supply special screwdrivers with a shoulder for this purpose.

General ordering data

Type	STB 14/D5/2.3/M3 SAK2.5
Order No.	0168600000
Version	SAK Series, Socket
GTIN (EAN)	4008190135225
Qty.	50 pc(s).

SAK Series
STB 14/D5/2.3/M3 SAK2.5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten
Dimensions and weights

Height	17.5 mm	Net weight	2.012 g
Diameter	5 mm		

Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Version	For the terminals		

Material data

Surface finish	galvanized	Material	Copper - zinc
Colour	Grey		

System specifications

Product family	SAK Series
----------------	------------

Classifications

ETIM 3.0	EC001134	UNSPSC	30-21-18-11
eClass 5.1	27-14-11-45	eClass 6.2	27-14-92-14
eClass 7.1	27-14-92-14		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

STEP	0168600000_01044_STB_14-D5-2.3-M3_SAK2.5_STP.stp
------	--