

**SAK Series**  
**TW SAKG46 HP/TF/GE/2****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com**Product image**

Similar to illustration

**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

Type	TW SAKG46 HP/TF/GE/2
Order No.	<a href="#">0179900000</a>
Version	SAK Series, Separation plate, yellow, 2 mm
GTIN (EAN)	4008190107833
Qty.	10 pc(s).

**SAK Series  
TW SAKG46 HP/TF/GE/2**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

Width	2 mm	Width (inches)	0.079 inch
Height	160 mm	Height (inches)	6.299 inch
Depth	70 mm	Depth (inches)	2.756 inch
Net weight	25.234 g		

**Temperatures**

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

**Material data**

Material	PA 66	Colour	yellow
UL 94 flammability rating	V-2		

**System specifications**

Version	Intermediate plate
---------	--------------------

**Additional technical data**

Installation advice	Direct mounting	Snap-on	No
---------------------	-----------------	---------	----

**Classifications**

ETIM 3.0	EC000886	ETIM 4.0	EC000886
ETIM 5.0	EC000886	ETIM 6.0	EC000886
UNSPSC	30-21-18-27	eClass 5.1	27-14-11-33
eClass 6.2	27-14-11-33	eClass 7.1	27-14-11-33
eClass 8.1	27-14-11-33	eClass 9.0	27-14-11-92
eClass 9.1	27-14-11-33		

**Approvals**

ROHS	Conform
------	---------