

**SAK Series, Accessories
EP 2 SAKG46/35 HP/TF/GE****Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

To guarantee a finger-proof level of safety when using modular terminals, open sides are covered with end or partition plates to prevent contact with live parts.

General ordering data

Type	EP 2 SAKG46/35 HP/TF/GE
Order No.	0180800000
Version	SAK Series, Accessories, End plate, Yellow, 2 mm
GTIN (EAN)	4008190006938
Qty.	10 pc(s).

SAK Series, Accessories EP 2 SAKG46/35 HP/TF/GE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	160 mm	Width	2 mm
Height	91 mm	Net weight	33.4 g

Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Additional technical data

Version	End and intermediate plate
---------	----------------------------

Dimensions

TS 32 offset	80 mm
--------------	-------

Material data

Material	PA 66	Colour	Yellow
UL 94 flammability rating	V-2		

System specifications

Product family	SAK Series, Accessories	Mounting rail	TS 35
----------------	-------------------------	---------------	-------

Classifications

ETIM 3.0	EC000886	UNSPSC	30-21-18-27
eClass 5.1	27-14-11-33	eClass 6.2	27-14-11-33
eClass 7.1	27-14-11-33		

Approvals

Approvals



ROHS	Conform
------	---------