

**SAK Series**  
**QL 4 SAKD2.5N**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Product image**


Similar to illustration

**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

Type	QL 4 SAKD2.5N
Order No.	<a href="#">0216000000</a>
Version	SAK Series, Cross-connector, for cross-connection link, No. of poles: 4
GTIN (EAN)	4008190118433
Qty.	50 pc(s).

## Data sheet

### SAK Series QL 4 SAKD2.5N

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Width	19.7 mm	Width (inches)	0.776 inch
Height	6 mm	Height (inches)	0.236 inch
Depth	1.5 mm	Depth (inches)	0.059 inch
Net weight	1.16 g		

### Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C		

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

### Material data

Material	Cu Zn	Colour	grey
----------	-------	--------	------

### System specifications

Version	for cross-connection link
---------	---------------------------

### Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

### Dimensions

Pitch in mm (P)	5 mm
-----------------	------

### Classifications

ETIM 3.0	EC000489	ETIM 4.0	EC000489
ETIM 5.0	EC000489	ETIM 6.0	EC000489
UNSPSC	30-21-18-01	eClass 5.1	27-14-11-40
eClass 6.2	27-14-11-40	eClass 7.1	27-14-11-40
eClass 8.1	27-14-11-40	eClass 9.0	27-14-11-40
eClass 9.1	27-14-11-40		

### Approvals

ROHS	Conform
------	---------