

## Conductor markers CLI C 02-3 GE/SW G MP

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

### General ordering data

|            |                                                                           |
|------------|---------------------------------------------------------------------------|
| Type       | CLI C 02-3 GE/SW G MP                                                     |
| Order No.  | <a href="#">0252111649</a>                                                |
| Version    | Conductor markers, 3 x 3.4 mm, PVC, soft, without Cadmium, Colour: Yellow |
| GTIN (EAN) | 4008190185251                                                             |
| Qty.       | 200 pc(s).                                                                |

## Conductor markers CLI C 02-3 GE/SW G MP

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |         |       |        |
|------------|---------|-------|--------|
| Length     | 3 mm    | Width | 3.4 mm |
| Height     | 4 mm    | Depth | 3.5 mm |
| Net weight | 0.045 g |       |        |

### General data

|                                   |                            |                                              |                    |
|-----------------------------------|----------------------------|----------------------------------------------|--------------------|
| Colour                            | Yellow                     | Colour of printing                           | Black              |
| Material                          | PVC, soft, without Cadmium | Material colour according to resistance code | 4                  |
| Operating temperature range, max. | 80 °C                      | Operating temperature range, min.            | -30 °C             |
| Orientation of print              | horizontal                 | Printed characters                           | Upper-case letters |
| Printing                          | G                          | Printing method                              | Laser print        |
| Recommended industries            | Process, Machinery         | Type of printing                             | Standard           |
| UL 94 flammability rating         | V-0                        |                                              |                    |

### Conductor and cable markers

|                               |                     |                               |                     |
|-------------------------------|---------------------|-------------------------------|---------------------|
| Conductor O.D., max.          | 3 mm                | Conductor O.D., min.          | 1 mm                |
| Conductor cross-section, max. | 1.5 mm <sup>2</sup> | Conductor cross-section, min. | 0.5 mm <sup>2</sup> |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001530    | UNSPSC     | 44-12-17-08 |
| eClass 5.1 | 27-14-91-03 | eClass 6.2 | 27-14-91-29 |
| eClass 7.1 | 27-14-91-29 |            |             |

### Approvals

|           |         |
|-----------|---------|
| Approvals |         |
| ROHS      | Conform |

### Conductor markers CLI C 02-3 GE/SW G MP

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Zeichnungen



Product is similar to illustration