

SAK Series, Accessories
QS 2/12/4**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Cross-connection plug types QS and DQS are used in conjunction with sockets for creating easily detachable cross-connections between modular terminals.

General ordering data

Type	QS 2/12/4
Order No.	0270760000
Version	SAK Series, Accessories, Cross-connector, for cross-connection link, No. of poles: 2
GTIN (EAN)	4008190011420
Qty.	20 pc(s).

SAK Series, Accessories QS 2/12/4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	20 mm	Width	12 mm
Height	34.5 mm	Net weight	7.1 g

Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Version	for cross-connection link		

Rated data

Rated current	44 A
---------------	------

Material data

Material	PA 66	Colour	Beige
UL 94 flammability rating	V-2		

System specifications

Product family	SAK Series, Accessories
----------------	-------------------------

Classifications

ETIM 3.0	EC000489	UNSPSC	30-21-18-01
eClass 5.1	27-14-11-40	eClass 6.2	27-14-11-40
eClass 7.1	27-14-11-40		

Product information

Descriptive text technical data	Current-carrying capacity max. 44 A
---------------------------------	-------------------------------------

Approvals

Approvals



ROHS	Conform
------	---------