

SAK Series
VH 17.5/5/3.5 SAK6N-16

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image

Similar to illustration

Klippon® Connect with clamping yoke Technology

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	VH 17.5/5/3.5 SAK6N-16
Order No.	0285200000
Version	SAK Series, Connecting sleeve, for cross-connection link, No. of poles:
GTIN (EAN)	4008190054717
Qty.	50 pc(s).

SAK Series

VH 17.5/5/3.5 SAK6N-16

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	5 mm	Width (inches)	0.197 inch
Height	5 mm	Height (inches)	0.197 inch
Depth	17.5 mm	Depth (inches)	0.689 inch
Net weight	1.46 g	Diameter	5 mm

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Material data

Material	Copper	Colour	grey
----------	--------	--------	------

System specifications

Version	for cross-connection link
---------	---------------------------

Additional technical data

Installation advice	Direct mounting	Type of fixing	when screwed in
---------------------	-----------------	----------------	-----------------

Dimensions

Diameter	5 mm
----------	------

Classifications

ETIM 3.0	EC000489	ETIM 4.0	EC000489
ETIM 5.0	EC000489	ETIM 6.0	EC002848
UNSPSC	30-21-18-11	eClass 5.1	27-14-11-45
eClass 6.2	27-14-92-14	eClass 7.1	27-14-92-14
eClass 8.1	27-14-92-14	eClass 9.0	27-14-11-92
eClass 9.1	27-14-11-92		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	STEP